

Hot water soluble Laundry bags made of PVA

For infectious laundry and contaminated work clothing

Odor-tight and resealable

Harmless to health and biodegradable

Meets the highest sanitary standards

Application:

Remove the bags individually, put the roll back in the closed bag immediately.

Wrap damp or wet laundry in dryer laundry.

Do not overfill sacks, max. 12 kg.

Do not tie sacks, but close them with the enclosed ribbon.

Store and transport filled sacks in a dry place.

Storage temperatures 7 ° -30 ° C.

Emptying before the wash cycle is not necessary, as the bag is completely put into the washing machine and works independently and completely at a washing temperature from 40 ° C / or 60 ° C and a washing time of at least

Dissolves 10 minutes without residue.

The use of some detergents may require higher washing temperatures to ensure solubility.

1 roll with 25 transparent bags in a resealable bag.

660 x 840 mm (approx. 87 liters), approx. 20 µ thick

Shelf life 12 months.

Use opened bags within 4 weeks if possible.